

Low Voltage Power Circuit Breaker Switchgear UL 1558

IEM's unique approach to engineering and manufacturing allows us to assemble products that meet specialized dimensional and electrical requirements.

Our flexible capabilities allow for the selection of industry leading components including control and measuring devices, allowing for a superior, fully customizable control and monitoring electrical assembly. This is just one element of IEM's superior control solutions to provide protection and operational reliability for any quality power distribution assembly.

Depending on the users' technical and physical requirements, UL 1066 power circuit breakers can be mounted in a fixed or drawout configuration. Indoor enclosures are available in an extensive selection of durable color finishes.

FEATURES & BENEFITS

- Voltage: up to 600V; Ampacity: up to 10,000A
- UL 1066 Circuit Breaker
- Through the door breaker operation
- Front accessibility to control and communication wiring
- Isolated access to all wiring
- All breakers have unique drawout design allowing for through-the-door racking
- Short-circuit withstand (4 cycle): Up to 200kA
- Short-time withstand (30-cycle): 65 kA, 85kA
- Bolted copper bus provided as standard

Full Customization and Design Flexibility

Component and Metering Selection Flexibility

Bus Based on Density Ratings

Seismic Tested to Worst Case Response Spectrum

Indoor Applications

UL or cUL Listed; Meets ANSI, IEEE, and NEMA Standards



Tradition. Technology. Innovation.

Low Voltage Switchgear UL 1558

Product Sheet
LV SWITCHGEAR UL 1558

FEATURES & BENEFITS (CONT'D)

- Large rear cable compartment pull area allowing maximum room for power cables
- Bus provision for future equipment expansion
- System designed for maximum uptime with low maintenance
- Modular circuit breaker designed for easy addition of control accessories
- Circuit breakers are available in various levels of interrupting ratings from 42–200kA at 635VAC
- Up to 4 circuit breakers can be mounted in a 24-inch wide section (up to 1600A frames), max 5000A per section
- Circuit breakers of like frame sizes and interrupting ratings are interchangeable
- 1558 switchgear can be integrated with our UL 1008 transfer switch equipment in a single lineup
- Service entrance and utility sections

SEISMIC RATING

Seismic testing completed – fully qualified to worst-case response spectrum.

IEM DIFFERENCE

All enclosures are designed for specific application with improved dimensional flexibility and finished using state of the art powder coating system providing an indoor finish that exceeds the 1500 hour salt spray testing requirement for outdoor equipment to 3000 hours.

Component and metering selections are based on value engineering for the application and optimized to meet specifications.

TECHNICAL SPECIFICATIONS

IEM Low Voltage Switchgear meets or exceeds applicable standards including UL1558, and ANSI C37.20.1.

IEM Low Voltage Switchgear meets seismic testing, circuit requirements as outlined by IEEE344 and ICC-ES-AC156.

Industrial Electric Mfg.™ (IEM)

Headquartered in Fremont, CA, IEM is the largest independent full-line manufacturer of electrical distribution and integrated control systems in the U.S. For over half a century, IEM has delivered customer-specific solutions to meet the ever changing power requirements of growth industries in North America. At IEM, tradition and technology still drive innovation. An experienced engineering staff and one of the most flexible design and manufacturing systems in the industry set IEM apart from standard product manufacturers.



Corporate Headquarters

Industrial Electric Mfg.™
48205 Warm Springs Blvd
Fremont CA 94539 USA
dir: +1.510.656.1600

Vancouver

Industrial Electric Mfg.™
3261 192 St.
Surrey, B.C. V3Z 1A7 CAN
dir: +1.866.302.9836

Jacksonville

Industrial Electric Mfg.™
3600 Port Jacksonville Parkway
Jacksonville FL 32226 USA
dir: +1.904.365.4444

www.iemfg.com